

## Han HPR HPTC size 3 CS-protection cover



Image is for illustration purposes only. Please refer to product description.

Part number	09 40 002 5412
Specification	Han HPR HPTC size 3 CS-protection cover
HARTING eCatalogue	<a href="https://harting.com/09400025412">https://harting.com/09400025412</a>

### Identification

Category	Accessories
Series of hoods/housings	Han® HPR HPTC
Type of accessory	Protection cover
Description of the accessory	for cable side

### Version

Locking type	Screw locking
--------------	---------------

### Technical characteristics

Tightening torque (screw locking)	5 Nm
Limiting temperature	-55 ... +85 °C
Degree of protection acc. to IEC 60529	IP65 IP66 IP67

### Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained



**Pushing Performance**  
Since 1945

## Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

## Commercial data

Packaging size	1
Net weight	150 g
Country of origin	Taiwan
European customs tariff number	85389099
GTIN	5713140902961
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467