

3550-40 UK

Torque wrench TORCOFLEX UK

1-550 Nm

Code **2958074** ETIM **EC002132**

EAN **4002805935583** UNSPSC **27-11-17-15**

Country of origin **Germany** eCI@ss **21-04-02-22**

Customs tariff number
82041100



Article description

- Adjustable, releasing and sturdy tubular torque wrench with integrated lever ratchet (from 3/4 inch with change disk) and with square drive for industry and the trades
- Classified to DIN EN 6789: 2017 type II class A calibrated to a max. admissible deviation of +/- 3 % and therefore more precise than +/- 4 % required by the standard
- Incl. test certificate according to DIN EN ISO 6789-2:2017
- For controlled clockwise tightening

Article information

Contents [Qty of pieces]	1	Torque range [min./max.] [N·m]	80 Nm - 400 Nm
Net weight [kg]	3,44 kg	Trigger mechanism	Short path triggering
Total length [mm]	740 mm	Precision +/-	+/- 3 %
Total width [mm]	69 mm	Direction of tightening	Right
Total height [mm]	65 mm	Fixed setting	no
Material	Steel tube construction with high-quality plastic parts	Test certificate	DIN EN ISO 6789-2:2017
Drive connector square (male)	3/4"	Graduation	10
Drive connector square (male)	20 mm	Head height 1 [mm]	36 mm
Return angle	7,2 °	Width of head 1 [mm]	68,0 mm
Number of teeth	50	Calibration length	634,2 mm
Drive type/drive	Reversible ratchet	vernier Nm	1 Nm
Torque (min.) [N·m]	80 Nm	Distance housing - square drive	34 mm
Torque (max.) [N·m]	400 Nm		