

FEATURES

- **Sintered Bronze Material:** Provides durability and resistance to wear, ensuring a long service life.
- **Flanged Design:** Offers secure positioning and easy installation in a variety of applications.
- **Dynamic Load Rating of 14 N/mm²:** Suitable for applications with moderate dynamic loads.
- **Static Load Rating of 50 N/mm²:** Capable of handling high static loads for increased reliability.
- **ISO 2795 and ISO 9001:2008 Certified:** Meets international standards for quality and performance.

RS PRO 22.02 mm Flanged Plain Bearing

RS Stock No: 529-058



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flanged plain bearing is designed for reliable performance in various industrial applications. Made from sintered bronze, it offers excellent durability and resistance to wear. Ideal for use in machinery where low maintenance and high efficiency are required.

General Specifications

Bore Size	22.02 mm
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	28.05 mm
Width	15 mm

Approvals

Standards/Approvals	ISO 2795, ISO 9001:2008, UKAS 001
---------------------	-----------------------------------