

4 Port USB 3.0 Hub plus 3 Dedicated USB Charging Ports (2 x 1A & 1 x 2A) - Wall Mountable Metal Enclosure

Product ID: ST4300U3C3



The ST4300U3C3 USB 3.0 Hub enables simultaneous data hub and USB charging functionality by adding three dedicated USB charge ports, as well as four USB 3.0 data ports, for a total of seven ports, all through a single USB 3.0 host connection.

The USB hub ports are compliant with the SuperSpeed USB 3.0 specification, offering data transfer rates up to 5 Gbps, and are backward compatible with USB 2.0 and 1.x specifications.

This externally powered USB hub also integrates 3 dedicated USB charging ports, providing 2 x 1A and 1 x 2A ports, enabling both data hub and USB charging station functionality. Support for USB Battery Charging Specification 1.2 lets you charge most mobile devices, including the Apple® iPhone®, iPad®, Microsoft® Surface™, Samsung Galaxy Tab™ and more.

Designed for easy access to the ports when connecting or disconnecting devices, the hub features an upright port orientation, in a compact and durable metal enclosure. For added flexibility, the hub includes a bracket for wall-mounted installations.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.



Certifications, Reports and Compatibility



Applications

- Use in IT helpdesk or tech bench environments to provide USB hub and charge ports for multiple devices
- Installation in locations where USB 3.0 ports need to be securely mounted to a surface, such as a wall or under a desk
- Expand your USB 3.0 capabilities at home or in the office

Features

- Provides 4 USB 3.0 hub ports, and 3 dedicated USB charging ports (2 x 1A, 1 x 2A)
- Supports USB Battery Charging Specification 1.2, including Apple® and Samsung Galaxy™ devices
- Compliant with SuperSpeed USB 3.0, with support for up to 5 Gbps
- Backward compatible with USB 2.0 and 1.x devices
- Compact, metal enclosure
- Includes wall-mount bracket

Hardware	Warranty	2 Years
	Bus Type	USB 3.0
	Chipset ID	VLI - VL812
	Fast-Charge Port(s)	Yes
	Industry Standards	USB Battery Charging Specification Rev. 1.2
	Ports	7
	USB-C Device Port(s)	No
	USB-C Host Connection	No
Performance	Maximum Data Transfer Rate	5 Gbps
	Type and Rate	USB 3.0 - 5 Gbit/s
Connector(s)	Connector Type(s)	1 - USB Type-B (9 pin) USB 3.0 Female 3 - USB Type-A (4 pin) USB 2.0 Female 4 - USB Type-A (9 pin) USB 3.0 Female
	OS Compatibility	OS Independent; No additional drivers or software required
	Special Notes / Requirements	Note
System and Cable Requirements		Available USB 3.0 port
Indicators	LED Indicators	1 - Power 4 - Hub Port Connection LEDs
	Power	Center Tip Polarity
Input Current		1.3 A
Input Voltage		100 ~ 240 AC
Output Current		3 A
Output Voltage		12 DC
Plug Type		M
Power Consumption (In Watts)		36
Power Source		AC Adapter Included
Environmental	Humidity	20~80% RH
	Operating Temperature	5°C to 35°C (41°F to 95°F)
	Storage Temperature	-20°C to 50°C (-4°F to 122°F)
Physical Characteristics	Color	Black

	Enclosure Type	Aluminum
	Form Factor	Desktop
	Product Height	24 mm [0.9 in]
	Product Length	110 mm [4.3 in]
	Product Weight	131 g [4.6 oz]
	Product Width	45 mm [1.8 in]
Packaging Information	Shipping (Package) Weight	558 g [19.7 oz]
What's in the Box	Included in Package	<p>1 - USB Charging Hub</p> <p>1 - USB 3.0 Cable</p> <p>1 - Wall Mount Bracket (w/ Screws)</p> <p>4 - Rubber Feet</p> <p>1 - Universal power adapter: comes ready for NA/EU/UK only when you buy in NA/EU/UK; comes ready for Australia and New Zealand only when you buy in Australia and New Zealand</p> <p>1 - Instruction Manual</p>

Product appearance and specifications are subject to change without notice.