



TECHNICAL DATA

OZZYJUICE® SW-4: HEAVY DUTY DEGREASING SOLUTION

A unique mixture of pH-neutral emulsifiers and surfactants containing no solvents. The heavy-duty formula is specifically designed to be versatile across all industries and applications whilst delivering exceptional performance. From automotive grease and varnishes to hydraulic fluid and bearing grease, SW-4 is a true multi-purpose, high performance degreaser that is ready for the toughest jobs.



FEATURES & BENEFITS:

- NSF A1 approved (165650)
- Bioremediating
- pH neutral
- Water based
- Non-hazardous, non-flammable
- Non-toxic, non-irritating
- Less expensive to use than solvent unit
- Reduces compliance costs

DIRECTIONS:

Add as supplied to the SmartWasher® as needed. Light comes on when the Smartwasher is low on OZZYJUICE®, see Operating manual for further instructions. Do not store below 0°C. Dispose of contents and container in accordance with local, regional, national and EU regulations.

APPLICATIONS:

Parts cleaning in preventative maintenance & repair facilities, industrial manufacturing plants, automotive repair shops, metal fabricators, and many more.

TYPICAL PRODUCT DATA

20 Litre Pail:	1032762
NSF A1:	165650
Appearance:	Orange liquid
Evaporation Rate:	Very slow
Flash Point:	None
pH:	8.0
Plastic Safe:	Yes
Specific Gravity:	1.02
VOC %:	<0.1
Optimal Working Temp (°C):	40 - 46 °C

OZZYJUICE DEGREASING/ CLEANING SOLUTIONS

Crude Oil:	Excellent
Hydraulic Trans. Fluid:	Excellent
Motor Oil:	Excellent
Solder & Flux:	Excellent
Bearing Grease:	Excellent
Automotive Grease:	Excellent
Resin Products:	Excellent
Fifth Wheel Grease:	Excellent
Creosote:	Excellent
Impacted Grease:	Excellent
Animal Fat:	Excellent
Automotive Varnish:	Good
Burned-On Carbon:	Excellent
Cutting Oils:	Good
Ink/Toner:	Good
Asphalt:	Good



Version Number: 2 Date of Issue: 28/04/2022 Date of Update: 29/10/2025



CRC INDUSTRIES EUROPE BV
 smartwashereurope.com
 SmartWasherEU@crcind.com
 SWtechsupport.emeia@crcind.com



SCAN HERE FOR
MORE INFO:

