



## DEWALT 54V XR FLEXVOLT Alligator Saw with 2x 54V XR FLEXVOLT Batteries

DCS397T2-GB

### Features:

- 54V XR FLEXVOLT Lithium-ion technology offers unrivalled cordless performance and power
- Brushless motor offers incredible efficiency and increased power delivery
- Heavy duty TCT blades which operate in opposite directions so that material does not move during cutting
- Aluminium constructed gear case for lighter weight
- Dust sealed gear case and bearings for increased durability and longevity of tool life
- Quick and easy blade changing system for reduced downtime
- Ergonomic bale and rear handle for superior support and reduction in fatigue



### Description:

The DEWALT 54V XR FLEXVOLT 430 mm Alligator Saw is part of the XR FLEXVOLT Lithium-ion platform offering unrivalled enhanced runtime and performance, heavy-duty construction applications can be completed without the need for mains power. The XR FLEXVOLT battery pack is not only interchangeable across the 54V power tools range, but is also backwards compatible with all existing DEWALT 18V XR tools, allowing professionals to be able to operate every tool they need on a single cordless system. It has been constructed with a high speed brushless motor which delivers high performance and power of up to 2400 strokes per minute. The brushless motor offers efficiency and increased power delivery, resulting in less wear and increased longevity of the tool. The Alligator saw is ideal for cutting Class 12 clay blocks such as poroton material.

### Supplied With:

- 2 x 54V XR FLEXVOLT Batteries
- 1 x TCT Class 12 blade
- 1 x Battery Charger

<b>Specifications</b>	
Battery	XR FLEXVOLT Lithium-Ion
Voltage	54 V
No Load Stroke Rate	0-2400 spm
Stroke Length	40 mm
Blade Length	43 cm
Length	918 mm
Height	219 mm
Weight	5.6 kg
Hand/Arm Vibration	4.1 m/s <sup>2</sup>
Sound Pressure	95 dB