



Quality Products. Service Excellence.

Type 4/4X, 6/6P Polycarbonate and ABS Plastic Enclosures 1557 Series

Water-Tight, Multiple Mounting Features



Key Features

- Ideally suited for mounting printed circuit boards or DIN rail mounted components (see photo features below for details).
- Can be used in a tabletop configuration or two different wall-mount configurations.
- Rounded corners and face provide a more modern look while still offering superior water-tight ratings.
- Available in black or gray ABS plastic
- ABS Versions are molded from general purpose material which carries a flammability rating of UL94-HB. For indoor use.
- Polycarbonate versions are UV stabilized for outdoor use and carry a UL94-5VA flammability rating. For indoor or outdoor use.
- Polycarbonate versions are cUL and UL 508A listed (File # E65324). ABS plastic versions are not UL listed.
- Gasketed lid with two piece "tongue & groove" construction provides protection against access of oil, dust and water.
- Gasket is one piece made from high temperature, U.L. listed silicone.
- ABS versions are designed to meet IP66
- Lid is secured with included M4 stainless steel machine screws which are threaded into integral stainless steel bushings for repetitive assembly & disassembly. All hardware is stainless steel to avoid corrosion caused by dissimilar metals.



Heavy Duty Wall Flange Mount (Mounting Feet Outward)



Flush Wall Mount (Mounting Feet as Keyhole Slots)



Desktop / Tabletop (Rubber Feet Included)



Accessories

- Pole Mount Kit
- Liquid-Tight Cordgrips (Nylon)

- Liquid-Tight Cordgrips (Nickel Plated Brass)
- Pressure Compensation Plug
- Breather Kit

Black ABS	Light Gray ABS	Black Polycarbonate (UL Listed)	Light Gray Polycarbonate (UL Listed)	Length	Width	Total Height	Replacement Gasket (2-pack)
1557BBK	1557BGY	1557B2BK	1557B2GY	80	80	45	1557BGASKET
1557BABK	1557BAGY	1557BA2BK	1557BA2GY	80	80	60	1557BGASKET
1557DBK	1557DGY	1557D2BK	1557D2GY	120	120	45	1557DGASKET
1557DABK	1557DAGY	1557DA2BK	1557DA2GY	120	120	70	1557DGASKET
1557FBK	1557FGY	1557F2BK	1557F2GY	160	160	45	1557FGASKET
1557FABK	1557FAGY	1557FA2BK	1557FA2GY	160	160	70	1557FGASKET
1557HBK	1557HGY	1557H2BK	1557H2GY	200	200	45	1557HGASKET
1557HABK	1557HAGY	1557HA2BK	1557HA2GY	200	200	70	1557HGASKET

Replacement Lid Screws (50-pack)

Part No.	SC576-50
----------	----------

PC Board Mounting Screws (50-pack)

Part No.	SC526-50
----------	----------

Replacement Rubber Feet (24-pack)

Part No.	1421T6CL
----------	----------

Replacement Wall Mounting Bracket Kits

Part Number (24-pack)	Color	Material
1557FOOTBK-24	Black	ABS Plastic
1557FOOTGY-24	Gray	ABS Plastic
1557FOOT2BK-24	Black	Polycarbonate
1557FOOT2GY-24	Gray	Polycarbonate

Pole Mount Bracket

1557 Enclosure	Pole Mount Kit (7" Max.)	Pole Mount Kit (15" Max.)	Screw type	Replacement Screw Pack
1557B	PMB5057WKIT1	PMB5057WKIT2	#8 x 1/2"	SCPMB4-20
1557BA	PMB5057WKIT1	PMB5057WKIT2	#8 x 1/2"	SCPMB4-20
1557D	PMB5057KIT3	PMB5057KIT4	#8 x 3/8"	SCPMB5-20
1557DA	PMB5057KIT3	PMB5057KIT4	#8 x 3/8"	SCPMB5-20
1557F	PMB6687KIT3	PMB6687KIT4	#8 x 3/8"	SCPMB5-20
1557FA	PMB6687KIT3	PMB6687KIT4	#8 x 3/8"	SCPMB5-20
1557H	PMB110127KIT3	PMB110127KIT4	#8 x 3/8"	SCPMB5-20
1557HA	PMB110127KIT3	PMB110127KIT4	#8 x 3/8"	SCPMB5-20

Data subject to change without notice