



## Main

|                            |   |
|----------------------------|---|
| Range of product           | OsiSense XC   |
| Series name                | Standard format   |
| Product or component type  | Limit switch lever  |
| Device short name          | ZCKY  |
| Product compatibility      | XCKL<br>XCKM<br>XCKS  |
| Associated head            | ZCKD05  |
| Movement of operating head | Rotary  |
| Type of operator           | Rod lever spring return metal (square rod 3 mm, L = 125 mm) |
| Type of approach           | Lateral approach  |

## Complementary

|                  |                    |
|------------------|--------------------|
| Switch actuation | By any moving part |
| Positive opening | Without            |

## Environment

|                                       |                                      |
|---------------------------------------|--------------------------------------|
| Ambient air temperature for operation | -25...70 °C for standard environment |
| Ambient air temperature for storage   | -40...70 °C for standard environment |
| Environmental characteristic          | Standard environment                 |

## Offer Sustainability

|                          |   |
|--------------------------|---|
| Sustainable offer status | Green Premium product   |
| RoHS (date code: YYWW)   | Compliant - since 1440 - Schneider Electric declaration of conformity<br><a href="#">Schneider Electric declaration of conformity</a> |
| REACH                    | Reference not containing SVHC above the threshold<br><a href="#">Reference not containing SVHC above the threshold</a>                |

---

|                                  |                                       |
|----------------------------------|---------------------------------------|
| Product end of life instructions | Need no specific recycling operations |
|----------------------------------|---------------------------------------|

---

**Contractual warranty**

---

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

---