

JGL13-1



Sample image

Order symbol : JGL13-1

EAN : 6418074300751

Product nr : 2550364

El. number :

Description : Hinged cover with inspection window

- Finland : 3424815
- Denmark : 8212007518
- Sweden : 2507774

Dimensions :	Height	Width	Depth
mm :	280	190	40
inch :	11.02	7.48	1.57

Materials :

Material :	Polycarbonate
Cover colour :	RAL 7035 -light grey
Gasket material :	Polyurethane

Ratings :

Ingress protection (EN 60529):	IP65;
Impact Resistance (EN 62262):	IK08;
electrical_insulation :	Not insulated
UV resistance :	-
Flammability Rating :	UL 94 V0
Glow Wire Test (IEC 695-2-1) °C :	960C

Temperatures :

Temperature °C (continuous) :	-40 ... 80
Temperature °F (continuous) :	-40 ... 175