



Metric Coarse Taps, Spiral Flute 40°

Tolerance	Class 2 for 6H fit
Surface Treatment	Bright or Blue
Chamfer No	3
Flute Geometry	Right Hand Spiral Flutes
Application	For tapping of blind holes.

Entry Code	M	P mm	l ₁ mm	l ₂ mm	d ₂ Ø mm	∇ a mm	l ₃ mm	Entry Code	M	P mm	l ₁ mm	l ₂ mm	d ₂ Ø mm	∇ a mm	l ₃ mm
E507M2	2	0,40	41	8	2,50	2,00	4	E507M10	10	1,50	80	18	10,00	8,00	11
E507M2BLUE	2	0,40	41	8	2,50	2,00	4	E507M10BLUE	10	1,50	80	18	10,00	8,00	11
E507M2.5	2,5	0,45	44,5	9,5	2,80	2,24	5	E507M12	12	1,75	89	22	9,00	7,10	10
E507M2.5BLUE	2,5	0,45	44,5	9,5	2,80	2,24	5	E507M12BLUE	12	1,75	89	22	9,00	7,10	10
E507M3	3	0,50	48	12,5	3,15	2,50	5	E507M14	14	2,00	95	24	11,20	9,00	12
E507M3BLUE	3	0,50	48	12,5	3,15	2,50	5	E507M14BLUE	14	2,00	95	24	11,20	9,00	12
E507M3.5	3,5	0,60	50	14	3,55	2,80	5	E507M16	16	2,00	102	24	12,50	10,00	13
E507M3.5BLUE	3,5	0,60	50	14	3,55	2,80	5	E507M16BLUE	16	2,00	102	24	12,50	10,00	13
E507M4	4	0,70	53	14	4,00	3,15	6	E507M18	18	2,50	112	29	14,00	11,20	14
E507M4BLUE	4	0,70	53	14	4,00	3,15	6	E507M18BLUE	18	2,50	112	29	14,00	11,20	14
E507M5	5	0,80	58	11	5,00	4,00	7	E507M20	20	2,50	112	29	14,00	11,20	14
E507M5BLUE	5	0,80	58	11	5,00	4,00	7	E507M20BLUE	20	2,50	112	29	14,00	11,20	14
E507M6	6	1,00	66	13	6,30	5,00	8	E507M22	22	2,50	118	29	16,00	12,50	16
E507M6BLUE	6	1,00	66	13	6,30	5,00	8	E507M22BLUE	22	2,50	118	29	16,00	12,50	16
E507M7	7	1,00	66	13	6,30	5,00	8	E507M24	24	3,00	130	35	18,00	14,00	18
E507M7BLUE	7	1,00	66	13	6,30	5,00	8	E507M24BLUE	24	3,00	130	35	18,00	14,00	18
E507M8	8	1,25	72	16	8,00	6,30	9								
E507M8BLUE	8	1,25	72	16	8,00	6,30	9								