

General	Product Name	RIVER 3 Max
	Capacity	572Wh/179200mAh
	Dimension	234×224×255 mm 9.2×8.8×10 in
	Net. Weight	8 kg/17.7 lb
Battery	Battery Chemistry	LFP (LiFePO4)
	Cycle Life	3000 Cycles to 80% Capacity
Output	AC Output	3 × 230V~50Hz, 600W Max (Surge 1200W, X-Boost 1200W)
	USB-A Output	2 × 5V=2.4A, 12W Per Port, Total 24W
	USB-C Output	1 × 100W 5/9/12/15V=3A Max, 20V=5A Max, 100W Max 1 × 140W 5V/9V/12V/15V=3A Max, 20V/28V=5A Max
	Car Output	1 × 12.6V, 10A, 126W Max
	Wireless	✗
Input	AC Recharge	200-240V, 3A Max, 50/60Hz, 650W 0-100% in 1.5 Hr
	Solar Recharge	11-55V, 13A, 220W Max 0-100% in 3.2 Hr (45W Input 0-100% in 15.6 Hr) (60W Input 0-100% in 11.7 Hr) (110W Input 0-100% in 6.4 Hr)
	Car Recharge	11-55V, 8A Max, 220W Max 0-100% in 6.5 Hr
	Generator Recharge	200-240V, 3A Max, 50/60Hz, 650W 0-100% in 1.5 Hr
	USB-C Recahrge	5V/9V/12V/15V=3A Max, 20V/28V=5A Max, 140W Max 0-100% in 7 Hr
Others	UPS	<10 ms
	EB	B300 (286Wh)
	APP	Wi-Fi & Bluetooth
	Noise	30 dB
	Waterproof	IP54 only for battery pack, not the whole package
	Warranty	5 Years
	EB Interface	
Rapid	Capacity	✗
	Dimension	✗
	Net. Weight	✗
	Input/output	✗
Environment Temperature	Optimal Operating Temperature	20°C-30°C (68°F-86°F)
	Charge Temperature	0°C-45°C (32°F-113°F)
	Discharge Temperature	-10°C-45°C (14°F-113°F)
	Storage Temperature	20°C-30°C (68°F-86°F)
Operating Altitude		≤2000 m
What's in the box		RIVER 3 Max AC Charging Cable Car Charging Cable USB-B to USB-A UPS Communication Cable Quick Start Guide and Warranty