



Wire Harness Tape – Hand-tearable Cloth Tape

HelaTape Protect 180

Features and Benefits

- High quality Polyester Fabric harnessing tape
- Rubber-based adhesive offers very good heat and media resistance
- High temperature stability from -40 °C to +125 °C
- Temperature resistance tested according to LV312
- Very good resistance against abrasion
- Material is very flexible and tearable by hand
- Excellent ageing resistance, stable against rotting



HelaTape Protect 180 is very flexible and used for cable harnessing.

MATERIAL	Polyester (PET)
Operating Temperature	-40 °C to +125 °C
Adhesion to Steel	3 N/10 mm
Adhesion to Backing	3 N/10 mm
Elongation at break	15 %
Breaking Strength	65 N/10 mm



HelaTape Protect 180

TYPE	Thickness (T)	Width (W)	Length (L)	Colour	Article-No.
HTAPE-PROTECT180	0.18	19.0	25.0 m	Black (BK)	712-10002

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.