

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0787324001](#)
Status: **Active**
Overview: [Compression Connectors](#)
Description: Compression Connector, Staggered contacts, 1.63mm Working Height, 4 Circuits

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	PCB Headers
Series	78732
Application	Board-to-Board, Signal
Comments	Contacts are staggered. Refer to sales drawings for varying pitch distances
Overview	Compression Connectors
Product Name	Battery Connector, Compression Connector
UPC	884982911826

Physical

Breakaway	No
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Durability (mating cycles max)	20
Glow-Wire Capable	No
Lock to Mating Part	None
Material - Metal	Titanium Copper
Material - Plating Mating	Gold over Nickel
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	0.032/g
Number of Rows	2
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.00mm, 2.00mm, 3.00mm
Plating min - Mating	0.381µm
Temperature Range - Operating	-40°C to +85°C
Termination Interface: Style	Surface Mount

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	30V


Solder Process Data

Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	REFLOW
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	245

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-78732-401
---------------	--------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/30/2017 (7 July 2017)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[78732 Series](#)