



Wide Blade Magnetic (Gen 2) 8m/26ft-35

WIDE BLADE MAGNETIC TAPE MEASURES (GEN 2)

- Longest Standout: Measure distances in the air of up to 5 m.
- Straightest Standout for more precise measurement of long distances in the air.
- The widest blade on the market at 35 mm provides more stability and stiffness of the blade.
- Finger-Stop feature for quick, controlled retraction of the blade.
- Improved blade durability with Double-Sided Anti-Tear coating for the first 15 cm of the blade.
- Long-lasting blade with full nylon extrusion coating.
- Impact resistant body for the toughest conditions on the job site.
- Double-Sided printing with vertical and horizontal scale for versatile measurements.
- Architectural scale to measure scaled drawings, such as blueprints.
- Strong magnetic hook for measuring in metallic environments.
- Available lengths: 5m, 5m/16ft, 8m, 8m/16ft.



Article Number	4932499210
Blade width (mm)	35
Length [m]	8 / 26ft
Magnetic	Yes
Pack quantity	1