


1692219 VZBA-2"-GGG-63-32L-F0507-V4V4T Ball valve - Series: All



1692219 VZBA-2"-GGG-63-32L-F0507-V4V4T Ball valve - Series: All

| Pos. | Part no. | Type | Note | Qty. | Unit |
|------|----------|---|--|------|------|
| A | 8001152 | VZBA-2"-GGG-...-V4V4T Set of wearing parts | Spare parts: 2, 3, 6, 7, 8 | 1 | PC |
| 1 | | | Not available Tightening torque 686.5 Nm / 506.3 lbf ft | 3 | PC |
| 2 | | | Not available separately, see position A | 3 | PC |
| 3 | | | Not available separately, see position A | 4 | PC |
| 4 | 721620 | VZBA-R2-63-32L-F-R Ball | | 1 | PC |
| 5 | | | Not available | 1 | PC |
| 6 | | | Not available separately, see position A | 1 | PC |
| 7 | | | Not available separately, see position A | 1 | PC |
| 8 | | | Not available separately, see position A | 2 | PC |
| 9 | | | Not available | 1 | PC |
| 10 | | | Not available | 2 | PC |
| 11 | | | Not available | 1 | PC |
| 12 | | | Not available | 1 | PC |
| 13 | | | Not available | 1 | PC |