


CONTACTUM



DD121SPMS

CONTACTUM



AWAITING IMAGE

Surge Device Spec:

Uc - 275V

In - 10kA

Imax - 20kA

Up - ≤ 1.2 kV

Green (ok) Red (replace) status indicator

12 Way 100A Switch + SPD

General

Box quantity: 1
ABC indicator: B
Colour: White

Technical

Associated standards: BS EN 61439-3
Rated voltage: 220-250V
Rated current: 100A
Frequency: 50-60Hz
Wiring system: 2 pole
Ambient operating temperature:
 -5 to 40°C (24hour average not exceeding 25°C)
Width in number of modular spacings: 16
Nature of supply: AC
DIN-rail: Yes
Extension possible: Yes
With lock: Optional
Type of cover: Hinged
Material housing: steel
Plate thickness cabinet: 1.2mm

Plate thickness door/cover: 1.2mm
Mounting method: Surface
Number of outgoing ways: 12

Copyright © 2017 Contactum Limited, Victoria House, 2 Blackmoor Lane, Croxley Green Business Park,
Watford, WD18 8GA

Source URL: <https://www.contactum.co.uk/content/dd121spms>