



Main

Range of product	Mureva Styl
Product or component type	Sealing membrane
Range compatibility	Mureva Styl
Colour tint	White (RAL 9003)

Complementary

Device mounting	Flush
Number of gangs	1 gang
Condition of use	Indoor/outdoor
Material	TPE (thermoplastic elastomer)
Length	71 mm
Height	26 mm
Width	71 mm
Chemical and detergent products resistance	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

IP degree of protection	IP44
IK degree of protection	IK08

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations