




MARKING: AWM E200765 STYLE 2725 60°C 30V 1P/28AWG AND 2C/28AWG USB FT2



Pin Assignment



Note:

1. Conductor material: Bare copper
2. Braid material: AL-MG braiding
3. Drain material: Tinned copper wire

ITEM NO	QTY	DESCRIPTION	COLOR
11. 99. 8752	10	VALUE USB2. 0 Cable, TypeAM-Micro BM, 1. 8m	white
11. 99. 8754	10	VALUE USB2. 0 Cable, TypeAM-Micro BM, 0. 8m	white
11. 99. 8755	10	VALUE USB2. 0 Cable, TypeAM-Micro BM, 3. 0m	white

④	MOLDING	OUTER MOLD: 45P PVC COLOR, white	9	G
③	USB-MICRO B	USB MICRO B MALE CONNECTOR FLASH GOLD ; NICKEL PLATED SHELL	1	SET
②	USB-AM	USB AMALE CONNECTOR FLASH GOLD ; NICKEL PLATED SHELL	1	SET
①	CABLE	USB CABLE 28AWG/1P+28AWG/2C+AL+BRAID(48*0.12mm AL-MG braiding) +Drain(7*0.12 Tinned copper wire)PVC JACKET OD: 3.8±0.2mm , COLOR: WHITE 433#	L	M
NO	P/N	DESCRIPTION	QTY	UNIT

REMARK NO	CHANG	SIGNATURE	DATE
DRAWN BY	MORGAN		SIGN
CHECKED BY			
AUDITED BY		APPROVED BY	QIJUNJIAN
CRAFT		DATE	2010. 12. 30



SCALE

USB AM/BMICRO-XXX

USB.AM.MICRO.XX.3