

Features

- Brass impellers
- Box with external capacitor
- Solids passage 35mm
- Pump body in AISI 304
- Pump shaft in AISI 420
- Suction and discharge in cast iron.
- O-rings in NBR/EPDM
- Double mechanical seal
- Float switch

RS PRO Water Pump

RS Stock No.: 0736543



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Submersible pump for wastewater, vortex system.
Evacuation, transfer and emptying of wastewater with solids in suspension.

General Specifications

Type	Drainage Systems Emergency Flood Kit Lifting Station Rainwater Harvesting Sewage Lifting Station Submersible Pump
Maximum Flow Rate	280 l/min
Input Connection	Free suction opening
Input Connection Size	-
Output Connection Size	G 1½"
Maximum Head	7m
Maximum Pressure	0,7bar
Body Material	AISI 304
Coupling Type	Integrated
Maximum Fluid Temperature	40°C
Head Type	Single
Noise Level	Not required
Auto On/Off Switch	Yes
Built-in Water Filter	No

Electrical Specifications

Phase	Single
Supply Voltage	230V – 50Hz
Input Power	0,9 kW

Mechanical Specifications

Dimensions	L 247 x W 189 x H 500 mm
Weight	14 kg

Protection Category

Safety Category Level	
IP Rating	IPX8
Insulation class	F

Classification

eCl@ss Version	
UNSPSC Version	

Approvals

Compliance/Certifications	EN 809, EN 60204-1, EN 60335-2-41, EN 50419, EN IEC 63000
Declarations	

Similar Products

Stock No.	Brand	Product Name	Maximum Flow Rate	Input Connection	Input Power
XXX-XXXX	RS PRO				
XXX-XXXX	RS PRO				

ADDITIONAL INFORMATION / DIAGRAMS / ILLUSTRATIONS /
ACCESSORIES