

Hedge Trimmer XGT®

UH006G

40Vmax • 600 mm

Compact hedge trimmer with high power for rough cutting.

XGT® powered Hedge trimmer has a wet guard which makes it water resistant. 3 - speed levels for optimum speed control. Reverse rotation system frees the blade when it is jammed by thick branches.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Strokes per Minute (SPM)	2000 / 3000 / 4000 min ⁻¹
Length Of Blade	600 mm
Max blade opening	25 mm
Tooth Spacing	38 mm
Continuous Use XGT® 40V Max / 4.0 Ah	65 / 110 / 195
Brushless Motor	✓
Sound Power Level (L _{WA})	92 dB(A)
Sound Pressure Level (L _{pA})	84 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Hedge Trimming	3,0 / ≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Hedge Trimming	1,5 m/s ²

User benefits

- Reliable cutting performance like petrol / AC hedge trimmers
- Optimum blade shape for smooth cutting and long run time
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- The no load continuous run time on a full battery charge is the same or longer than that on a full tank of petrol
- Double action switch for increased safety
- Constant speed control maintains constant speed under load
- Reverse rotation system frees the blade when it is jammed by thick branches
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makita.uk.com



Related products

■ Optional AC

197439-7

Grease Vessel Set



■ Other

User manual

Parts drawing