

Main

Range	Acti9
Product name	Acti9 SBI
Product or component type	Fuse-disconnector
Device short name	SBI
Poles description	3P + N



Complementary



[In] rated current	10 A 12 A 16 A 20 A 25 A 32 A 40 A 50 A
Fuse curve	AM GG
Fuse size	14 x 51 mm
[Ue] rated operational voltage	690 V AC
Mounting support	35 mm symmetrical DIN rail
Locking options description	Non padlockable
9 mm pitches	12
Height	107 mm
Width	106 mm
Depth	70 mm
Connections - terminals	Screw clamp terminals (top or bottom) 1 cable(s) 1...16 mm ² rigid Screw clamp terminals (top or bottom) 1 cable(s) 1...10 mm ² flexible Screw clamp terminals (top or bottom) 1 cable(s) 1...10 mm ² flexible with ferrule
Wire stripping length	10 mm for top or bottom connection
Tightening torque	2.2 N.m top or bottom

Environment

Standards	IEC EN 60947-3
Pollution degree	3
Ambient air temperature for operation	-20...60 °C
Ambient air temperature for storage	-40...80 °C

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration