

## VDE 2170 2,5

### VDE Screwdriver

for slotted head screws

|                       |             |
|-----------------------|-------------|
| Code                  | ETIM        |
| 1612220               | EC000158    |
| EAN                   | UNSPSC      |
| 4010886826003         | 27-11-17-01 |
| Country of origin     | eCl@ss      |
| Slovenia              | 21-04-04-01 |
| Customs tariff number |             |
| 82054000              |             |



### Article description

- Individually tested, VDE insulation up to 1000 V, acc. to EN 60900/IEC 60900, fully insulated blade
- Tip as per DIN ISO 2380-1 Form A
- 3-component Power-Grip<sup>3</sup> handle with suspension hole
- Ergonomic handle shape for accurate, non-tiring work
- Positive connection of handle and blade for optimum power transmission
- Type of drive marked at the end of the handle
- Blade of galvanised molybdenum-vanadium steel

### Article information

|                          |                           |                               |                                              |
|--------------------------|---------------------------|-------------------------------|----------------------------------------------|
| Contents (Qty of pieces) | 1                         | Impact cap                    | no                                           |
| Version/Execution        | with hanging hole         | Cap rotatable                 | no                                           |
| Net weight [kg]          | 0,038 kg                  | Anti-magnetic                 | no                                           |
| Total length [mm]        | 160 mm                    | Ball head                     | no                                           |
| Total width [mm]         | 28 mm                     | Handle available              | yes                                          |
| Total height [mm]        | 24 mm                     | Isolated                      | yes                                          |
| Material                 | Molybdenum-vanadium-steel | Corrosion Protected           | no                                           |
| Blade length             | 75 mm                     | Colour coding                 | no                                           |
| Standard                 | EN 60900/IEC60900         | Unit-tested                   | yes                                          |
| Blade width [mm]         | 2,5 mm                    | Handle design                 | 3-component grips VDE insulated up to 1000 V |
| Low sparking design      | no                        | Output tip reference standard | DIN ISO 2380-1 - Form A                      |
| Blade shape              | Round                     | Drive hexagon                 | no                                           |
| Roll protection          | yes                       | Blade thickness               | 0,4 mm                                       |