

# Rittal – The System.

Faster – better – everywhere.



## VX 5302.155

## 482.6 mm (19") mounting angles, dynamic

State: 9/12/2025 (Source: [rittal.com/uk-en](http://rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 5302.155 - 482.6 mm (19") mounting angles, dynamic for VX IT

Mounting angles, also for accommodating server system installation kits.

## Features

|                          |                                                                                                                                                                                                                                                                                   |
|--------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No.                | VX 5302.155                                                                                                                                                                                                                                                                       |
| Design                   | for VX IT 482.6 mm (19") mounting angles, dynamic                                                                                                                                                                                                                                 |
| Product description      | Suitable for assembling a 482.6 mm (19") mounting level or for 482.6 mm (19") partial installation. The L-shaped design can directly accommodate all commercially available mounting kits for server systems, which are fastened directly to the 482.6 mm (19") system punchings. |
| Benefits                 | Integral, bidirectional U labelling<br>Integral system punchings on a U pitch pattern on the front and sides, allows U-specific mounting of cable routing components for structured cabling                                                                                       |
| Technical specifications | Side punchings, round and square, on a U pitch pattern<br>Potential equalisation within the mounting level and with the locating frame is achieved via the assembly components<br>482.6 mm (19") mounting hole including U centre fixing attachment to standard EIA 310 E         |
| Applications             | For mounting a 482.6 mm (19") mounting level within the VX IT rack system                                                                                                                                                                                                         |
| Material                 | Sheet steel, 2.5 mm                                                                                                                                                                                                                                                               |
| Surface finish           | Primed                                                                                                                                                                                                                                                                            |
| Colour                   | RAL 9005                                                                                                                                                                                                                                                                          |
| Supply includes          | Assembly parts                                                                                                                                                                                                                                                                    |
| Mounting position        | rear                                                                                                                                                                                                                                                                              |
| Installation options     | Alternative installation widths from 21" – 24", depending on the mounting variant and rack dimensions selected                                                                                                                                                                    |

# Features

|                               |                                                                                                                                                                        |
|-------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Assembly instruction          | To be combined with cross-member, depth stays or mounting bracket for attachment<br>Use of the different mounting options depends on the relevant enclosure dimensions |
| To fit                        | Height: = 42 U                                                                                                                                                         |
| Packs of                      | 2 pc(s).                                                                                                                                                               |
| Net weight                    | 13.16                                                                                                                                                                  |
| PCF per pack (cradle-to-gate) | 52 kg CO2 eq (Cat B)                                                                                                                                                   |
| Note on PCF category          | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared                                                         |
| Customs tariff number         | 73269098                                                                                                                                                               |
| EAN                           | 4028177955561                                                                                                                                                          |
| ETIM 9                        | EC002620                                                                                                                                                               |
| ECLASS 8.0                    | 27189261                                                                                                                                                               |