

632.3217-R**DISTRIBUTION ASSEMBLY**
IP44 3P+N+E 32A 400V

* Product image may be indicative



EN 61439-3 (2012-04)

Low voltage direct. 2014/35/EU
EMC directive 2014/30/EU**■ GENERAL CHARACTERISTICS**

Commercial Series	BLOCK Series
Synthetical description	DISTRIBUTION ASSEMBLY
Mounting version	SURFACE MOUNTING

■ TECHNICAL CHARACTERISTICS

Rated current	32A
Rated voltage	400V
Working frequency	50Hz
	60Hz
Poles	3P+N+E
Hour position	6h
Inlet supply unit	Terminal block 6mm ²
RCD protection	Main switch with RCD

■ PHYSICAL CHARACTERISTICS

Material	THERMOPLASTIC
Protection degree IP	IP44
Protection degree IK	IK08
Mounting version	SURFACE MOUNTING
Typology	Stationary distrib.assemblies
Version	With protection appliance

■ DIMENSIONAL CHARACTERISTICS

No. of available outlets	1 NR
--------------------------	------

■ DOWNLOAD

Wiring diagram
Technical drawing [PDF]
Technical drawing [STP]
Technical drawing [DWG]