Features

- ChA, ChB Counting, Reset, Pause Input
- Fast Speed Counter
- 6 Digits (PV) Display
- 230Vac Power Supply
- ModBus RS-232 RTU Serial Communication
- 96X48mm Panel Dimension

RS PRO High Speed Counter

RS Stock No:
874208



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

High Speed Counter:

- 2X Input (ChA, ChB)
- 2X Relay Output (5A@250Vac)
- Input Frequency Max. 200kHz
- Reset and Pause Input
- Sensor Supply Voltage 12Vdc
- ModBus RS-232 RTU Communication

General Specifications

Supply Voltage and Power	230Vac 50/60Hz – 2,5A
Sensor Inputs	Reset, Pause and ChA-ChB Counting Inputs
Relay Outputs	2X Relay Output (5A@250Vac)
Communication	ModBus RS-232 RTU

Mechanical Specifications

Dimension	96 mm x 48 mm 86,5 mm
Panel	IP65 at front, IP20 at rear
Max. Operating Temperature / Humidity	50°C / 90 % max. (None condensing)

Electrical Connection

