

Features

- 1/4" drive inch 6 point sockets is more powerful tightening, preserves fastners
- Finishing bright chrome and available as rack set

RS PRO 1/4 IN Drive Standard Socket, 6 Point



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO 1/4 IN Drive Standard Socket, 6 Point

Introducing 1/4" drive hexagon imperial sockets from our own brand RS PRO, a selection of high quality and reliable 6-point sockets to choose from, designed for use with wrench and turning tools with a 1/4" drive.

The sockets are manufactured from chrome vanadium steel, providing a durable socket that can withstand extensive use in a range of environments. The sockets also feature a mirror chrome finish offering a stylish and professional aesthetic whilst offering excellent corrosion resistance properties. RS PRO 1/4" sockets are available in a variety of metric sizes and make an excellent addition to any socket set, ideal for applications requiring nuts and bolts to be tightened and loosened by hand.

The hexagon sockets securely fit to a range of fasteners such as nuts and bolts, enhancing the grip and torque whilst allowing you to work quickly with ease.

Features and Benefits

- Available in a variety of sizes ranging from 3/16in to 9/16in
- Manufactured from chrome vanadium steel offering enhanced strength and durability
- Mirror chrome finish providing a professional aesthetic with corrosion resistance
- Suitable for a wide range of applications
- Hexagon socket to provide a secure grip and torque with nuts and bolts
- Suitable for 1/4" drive wrenches
- DIN 3124, TS ISO 2725-1

General Specifications

Socket Size	See details below
Imperial or Metric	Imperial
Drive Size	1/4 in
Socket Type	Standard Socket
Socket Head Type	6 point
Length	See details below
VDE/1000V Approved	No
Non Sparking	No
Finish	Chrome
Overall Length	25mm
Material	Chrome Vanadium Steel
Drive Type	Square

Stock No.	Brand	Product Name	Socket Size	Length
0441040	RS PRO	1/4 IN DR SHORT SOCKET 6PT	3/16 IN	25mm
0441042	RS PRO	1/4 IN DR SHORT SOCKET 6PT	7/32 IN	25mm
0441043	RS PRO	1/4 IN DR SHORT SOCKET 6PT	1/4 IN	25mm
0441045	RS PRO	1/4 IN DR SHORT SOCKET 6PT	9/32 IN	25mm
0441046	RS PRO	1/4 IN DR SHORT SOCKET 6PT	5/16 IN	25mm
0441047	RS PRO	1/4 IN DR SHORT SOCKET 6PT	11/32"IN	25mm
0441049	RS PRO	1/4 IN DR SHORT SOCKET 6PT	3/8 IN	25mm
0441051	RS PRO	1/4 IN DR SHORT SOCKET 6PT	7/16 IN	25mm
0441052	RS PRO	1/4 IN DR SHORT SOCKET 6PT	1/2 IN	25mm
0441053	RS PRO	1/4 IN DR SHORT SOCKET 6PT	9/16 IN	25mm

Approvals

Declarations	REACH DoC
Standards Met	DIN 3124, ANSI

Similar Products

Stock No.	Brand	Product Name	Socket Type	Drive Size	Socket Size	Socket Head Type
0441040	RS PRO	1/4 IN DR SOCKET	Standard Socket	1/4 IN	3/16 IN	6 Point
0441042	RS PRO	1/4 IN DR SOCKET	Standard Socket	1/4 IN	7/32 IN	6 Point
0441043	RS PRO	1/4 IN DR SOCKET	Standard Socket	1/4 IN	1/4 IN	6 Point
0441045	RS PRO	1/4 IN DR SOCKET	Standard Socket	1/4 IN	9/32 IN	6 Point
0441046	RS PRO	1/4 IN DR SOCKET	Standard Socket	1/4 IN	5/16 IN	6 Point
0441047	RS PRO	1/4 IN DR SOCKET	Standard Socket	1/4 IN	11/32 IN	6 Point
0441049	RS PRO	1/4 IN DR SOCKET	Standard Socket	1/4 IN	3/8 IN	6 Point
0441051	RS PRO	1/4 IN DR SOCKET	Standard Socket	1/4 IN	7/16 IN	6 Point
0441052	RS PRO	1/4 IN DR SOCKET	Standard Socket	1/4 IN	1/2 IN	6 Point
0441053	RS PRO	1/4 IN DR SOCKET	Standard Socket	1/4 IN	9/16 IN	6 Point
0441055	RS PRO	1/4 IN DR DEEP SOCKET	Deep Socket	1/4 IN	5/16 IN	6 Point
0441056	RS PRO	1/4 IN DR DEEP SOCKET	Deep Socket	1/4 IN	3/8 IN	6 Point
0441058	RS PRO	1/4 IN DR DEEP SOCKET	Deep Socket	1/4 IN	7/16 IN	6 Point
0441059	RS PRO	1/4 IN DR DEEP SOCKET	Deep Socket	1/4 IN	1/2 IN	6 Point
0441061	RS PRO	1/4 IN DR DEEP SOCKET	Deep Socket	1/4 IN	9/16 IN	6 Point
0441062	RS PRO	3/8 IN DR SHORT SOCKET	Standard Socket	3/8 IN	7/16 IN	12 Point
0441064	RS PRO	3/8 IN DR SHORT SOCKET	Standard Socket	3/8 IN	1/2 IN	12 Point
0441065	RS PRO	3/8 IN DR SHORT SOCKET	Standard Socket	3/8 IN	9/16 IN	12 Point
0441067	RS PRO	3/8 IN DR SHORT SOCKET	Standard Socket	3/8 IN	5/8 IN	12 Point
0441068	RS PRO	3/8 IN DR SHORT SOCKET	Standard Socket	3/8 IN	3/4 IN	12 Point
0441069	RS PRO	3/8 IN DR DEEP SOCKET	Deep Socket	3/8 IN	5/16 IN	12 Point
0441070	RS PRO	3/8 IN DR DEEP SOCKET	Deep Socket	3/8 IN	3/8 IN	12 Point

Stock No.	Brand	Product Name	Socket Type	Drive Size	Socket Size	Socket Head Type
0441071	RS PRO	3/8 IN DR DEEP SOCKET	Deep Socket	3/8 IN	7/16 IN	12 Point
0441073	RS PRO	3/8 IN DR DEEP SOCKET	Deep Socket	3/8 IN	1/2 IN	12 Point
0441074	RS PRO	3/8 IN DR DEEP SOCKET	Deep Socket	3/8 IN	9/16 IN	12 Point
0441075	RS PRO	3/8 IN DR DEEP SOCKET	Deep Socket	3/8 IN	11/16 IN	12 Point
0441077	RS PRO	1/2 IN DR SHORT SOCKET	Standard Socket	1/2 IN	9/16 IN	12 Point
0441078	RS PRO	1/2 IN DR SHORT SOCKET	Standard Socket	1/2 IN	5/8 IN	12 Point
0441080	RS PRO	1/2 IN DR SHORT SOCKET	Standard Socket	1/2 IN	11/16 IN	12 Point
0441081	RS PRO	1/2 IN DR SHORT SOCKET	Standard Socket	1/2 IN	3/4 IN	12 Point
0441083	RS PRO	1/2 IN DR DEEP SOCKET	Deep Socket	1/2 IN	9/16 IN	12 Point
0441084	RS PRO	1/2 IN DR DEEP SOCKET	Deep Socket	1/2 IN	5/8 IN	12 Point
0441086	RS PRO	1/2 IN DR DEEP SOCKET	Deep Socket	1/2 IN	11/16 IN	12 Point
0441087	RS PRO	1/2 IN DR DEEP SOCKET	Deep Socket	1/2 IN	3/4 IN	12 Point