


Datasheet**Stock No: 230-122****RS Pro Nylon****Product Details****Slotted Angle Accessories**

A range of accessories for use with slotted construction angle. Tension plates: aid structural rigidity. Must be used with 1 1/2 in.x1 1/2 in. angle. Nuts and bolts: 5/16 in. zinc plated steel nuts and bolts. Plastic feet: used to protect surfaces from scratching. Available for single uprights. Castors: (supplied in sets of 4). 65mm nylon (2 swivel:2fixed) fitted to steel fixing plates. Maximum castor loading, set of 4 = 218kg

Slotted Construction Angle System

A versatile construction material which is simple and easy to use and may be adapted to suit individual applications. Just cut and bolt angle together, no painting, welding or drilling required. With the range of accessories available a variety of items may be constructed including trolleys, workbenches, partitions, shelving, workframes, etc. Slotted angle is also used in the building industry for constructional supports for service piping, ventilation ducting, cable trays, trunking, suspended ceilings and timber studding.



ENGLISH

Specifications:

Load Capacity

218kg

Material

Nylon, Steel