




Datasheet

RS 2A Radial F Leaded PCB Mount Fuse, 250 V ac RS Stock 611-0664




SRF RoHS I-T CHARACTERISTICS CURVE

Dimensions: (mm)



MATERIALS: THERMOPLASTIC, UL94-V0



Specifications:

BREAKING CAPACITY:
CCC/SEMKO/VDE: 35A OR 10In WHICHEVER IS GREATER
UR/CSA/PSE: 100A 250V AC

ELECTRICAL CHARACTERISTICS:

RATING		BLOWING TIME
2.1In	Max	30min
2.75In	Min	10ms
	Max	3sec
4In	Min	3ms
	Max	300ms
10In	Max	20ms