

# XCKD2118N12

Limit Switch , Lever Arm with Thermoplastic Roller (ZCY18)



List Price \$94.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

## Technical Characteristics

Actuation	CW and CCW
Actuator Action	Momentary
Actuator	Lever Arm with Thermoplastic Roller (ZCY18)
Head Type	Rotary (ZCE01)
Operating Torque/Force	14.16 Inch-Ounces (0.10Nm)
Marketing Trade Name	OsiSense
Lever Arm Length	33mm
Maximum Actuation Speed	1.5 m/s
Roller Dimension	19 x 5.5mm
Type	XCKD
Type of Duty	General Duty
RoHS	Yes
Body Type	Compact Modular (ZCD21)
Shock Resistance	50G
Body Material	Metal
Vibration Resistance	25G
Weight	0.496 lbs (0.225kg)
Connection Type	Conduit Entrance (0.5" NPT)
Contact Configuration	1 N.O./1 N.C.
Contact Operation	Snap Action
Positive Opening	Yes
Terminal Type	Screw Clamp
Ampere Rating	10A
Maximum Voltage Rating	240VAC/250VDC
NEMA Enclosure Rating	NEMA 1/2/4/6/12/13
Degree of Protection	IP66/67
Operating Temperature Range	-13 to 158°F (-25 to 70°C)
Approvals	UL Listed - CSA Certified - CE Marked
Conforming to Standards	CENELEC EN 50047

## Shipping and Ordering

Category	22418 - Limit Switches, Medium Duty, Compact, IEC, Type XCKP & XCKT
----------	---

Generated: 07/13/2010 15:57:31

Discount Schedule	T
GTIN	00785901300519
Package Quantity	1
Weight	0.51 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	MX

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.