



DW310K

1200 Watt Heavy Duty Reciprocating Saw

Selling Proposition

- 1200 Watt motor delivers increased power for heavy duty applications
- 0 - 2,600 SPM and 28 mm stroke length for fast and efficient cutting
- Keyless adjustable shoe easily adjusts the depth of cut and extends the blade life
- Variable speed trigger provides control and versatility
- Keyless stainless steel blade change for quick and easy blade changes and increased reliability

Standard Equipment

- Heavy duty carrying case

Warranty Specifications

- 1 Year Free Service Contract
- 1 year full warranty
- 30 Day No Risk Satisfaction Guarantee

| Specifications | |
|--|------------|
| Power Input | 1200 Watts |
| Power Output | 630 Watt |
| No Load Stroke Rate | 0-2600 spm |
| Stroke Length | 28 mm |
| Max. Cutting Capacity [Wood] | 300 mm |
| Max. Cutting Capacity [Steel Sections & Pipes] | 130 mm |
| Max. Cutting Capacity [PVC] | 160 mm |
| Weight | 4.0 kg |