



XS605R1NBM08

Miniature inductive sensor, M5, L39mm, stainless, Sn1.5mm, M8 connector

COMMERCIALISED

Main

Range of product	Telemecanique Inductive proximity sensors XS
Series name	miniature format
Sensor type	inductive proximity sensor
Sensor name	XS6
Sensor design	cylindrical M5
Size	38 mm
Body type	fixed
Type of output signal	discrete
Wiring technique	3-wire
Discrete output function	1 NC
Detector flush mounting acceptance	quasi flush mountable
Discrete output type	NPN
Material	stainless steel
Electrical connection	Male connector M8, 3 pins
Output circuit type	DC
[Us] rated supply voltage	12...24 V DC with reverse polarity protection
Switching capacity in mA	<= 100 mA DC with overload and short-circuit protection

Complementary

Enclosure material	stainless steel 303
Detection face	frontal
Thread type	M5 x 0.5
Front material	PBT
Differential travel	1...20 % of Sr

Status LED	Output state: 1 LED (yellow)
Switching frequency	<= 5000 Hz
Voltage drop	<1,5V
Current consumption	<= 10 mA no-load
Delay first up	50 MILLISECOND
Marking	CE UKCA

Environment

Product certifications	cULus
Shock resistance	conforming to IEC 60947-5-2

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither TMSS Holding nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Updated: 28/02/2025

