

## Features

- For use with compressed air in workshops, garages, assembly line and industrial applications.
- Internal steel frame and drum encased in a durable polypropylene outer cover.
- PU Mesh Hose
- Auto lock/Auto rewind
- Automatic Spring Return.
- Adjustable Hose Stop
- 180 ° degree swivel bracket.
- Wall or ceiling mounted.
- Supplied with 1.5m of leader hose.
- For use with air tools, spray equipment, blow guns etc.

## RS PRO Family Name

RS Stock No.: 0325313



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

### RS PRO Compact Heavy Duty Air Hose Reel

- For use with compressed air in workshops, garages, assembly line and industrial applications
- Unique Design
- Internal steel frame and drum encased in a durable polypropylene outer cover.
- PU Mesh Hose
- Auto lock/Auto rewind
- Automatic Spring Return
- Adjustable Hose Stop
- 180 ° degree swivel bracket
- Wall or ceiling mounted.
- Supplied with 1.5m of leader hose.
- For use with air tools, spray equipment, blow guns etc.
- Hose is stored safely in a convenient place ready for use.

## General Specifications

Hose Length	10m
Hose Inner Diameter	10mm
Hose Outer Diameter	13.5mm
Mounting	Wall Mounted
Inlet Connection	¼" BSP Male
Outlet Connection	¼" BSP Male

## Mechanical Specifications

Operating Pressure	Max. 16 Bar
Retraction Operation	Spring Return
Weight	5kg

## Specifications

NO	PRODUCT NAME	QTY	NO	PRODUCT NAME	QTY	NO	PRODUCT NAME	QTY	NO	PRODUCT NAME	QTY
1	Spring and spring fastening lock	1	12	Latch lever axle	1	23	Right plastic shell	1	34	NUT M6	1
2	Spring and Shaft connection spring	1	13	one-way latch lever	1	24	SCREW M4x50	2	35	Safety pin	1
3	Spring	1	14	External circlip	1	25	NUT M4	4	36	NUT M12	1
4	Reel inside	1	15	Outlet three way valve	1	26	locating pin spring	1	37	Inlet three way valve	1
5	Axle copper sleeve	1	16	Left plastic shell	1	27	locating pin support	1	38	Inlet pipe	1
6	Reel inside cover	2	17	protective	2	28	locating pin knob	1	39	Inlet three way valve guard	1
7	O RING 16x2.4	2	18	Cross flat head screw M4x14	2	29	Round head cross head screw M3x10	1	40	SCREW 4x16	2
8	O RING 12x2.4	2	19	Round cross head screw M4x12	6	30	Support copper sleeve	2	41	Outlet pipe	1
9	Axle	1	20	roller shaft	2	31	Support	1	42	Stop ball	1
10	Latch lever	1	21	roller	2	32	Screw M6x25	1	43	Screw 5x16	2
11	Latch lever spring	1	22	Positioning pin guide sleeve	1	33	6X35 rod	1	44	Holder	1

