

## FEATURES

- Malleable iron construction
- Ergonomic Red Vinyl grip for your comfort
- Toggle Press is machined base and frame
- Tapped holes in base for tool mounting
- Hardened pins and bushes

# RS PRO 1.2t Manual Toggle Press

RS Stock No.: 254-850



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

RS PRO Manual Toggle Press is designed in mind for light/medium-duty work such as forming, swaging, riveting, marking, piercing and assembly.

254-850 - Medium-duty, Manual Toggle Press, 1200 kg

254-844 - Medium-duty, Manual Toggle Press, 600 kg

### General Specifications

<b>Type</b>	Manual Toggle Press
<b>Output Pressure</b>	1.2t
<b>Application</b>	Riveting, Staking, Crimping, Marking, High force numbering, High force stamping, Stroke cutting, Piercing, Punching, Shearing, Embossing, Gluing

### Mechanical Specifications

<b>Height</b>	290mm
<b>Base Width</b>	120mm





