

DATA SHEET



✓ Highlights

- Coloured paste with flexible stroke width - up to a maximum of 10 mm
- Long-lasting indoors and outdoors
- Exceptional ink for heat-resistant marks up to 300 °C
- Visible marking even in compromised lighting conditions
- Ready to use
- Intensive colours
- High-quality brand product

edding 950 industry painter yellow

- Industry paste marker for highly permanent marking on rusty or rough surfaces of materials like metal, stone and wood
- The colour paste has a stroke width of up to 10 mm
- Paste markers with twist-out wax-like nib
- The highly opaque and highly permanent colour paste is waterproof, smudge-proof and extremely lightfast
- Can even be used for writing on clean surfaces under water

Art.No. **4-950005**

GTIN **4004764019670**



DATA SHEET



Specifications

Model	e-950
Shape of nib	Round nib
Stroke width	10 mm
Colour	Yellow
Included colours	Yellow
Number of available colours	5
Applicable on	Rubber, Glass, Wood, Metal/Steel/Iron, Concrete/Stone
Ink description	Highly opaque, highly permanent colour paste
Permanent	Yes
Lightfast	Yes
Opaque	Yes
Low odour	Yes
Waterproof	Yes
Refillable	No
Quick drying	No
Material of barrel	Polypropylene (PP)
Material of cap / mouthpiece	Polypropylene (PP) / -

Logistics

GTIN	4004764019670
Article number	4-950005
Customs tariff number	960910900000
Quantity	1 piece(s)
Packing dimensions	21 x 21 x 131 mm
Weight (gross/net)	30.67 g / 27 g
Country of origin	Japan

DATA SHEET

Product overview

Article name	Article number	GTIN/EAN	Minimum order quantity
edding 950 industry painter blister of 1 black	4-950-1-4001	4004764894970	5
edding 950 industry painter blister of 1 yellow	4-950-1-4005	4004764895038	5
edding 950 industry painter blister of 1 white	4-950-1-4049	4004764895069	5
edding 950 industry painter black	4-950001	4004764019649	10
edding 950 industry painter red	4-950002	4004764019656	10
edding 950 industry painter blue	4-950003	4004764019663	10
edding 950 industry painter yellow	4-950005	4004764019670	10
edding 950 industry painter white	4-950049	4004764019687	10