
PRODUCT-DETAILS

TY537M

CBL TIE 120LB 14IN NAT NYL MNTG HOL



General Information

Extended Product Type	TY537M
Product ID	7TAG009520R0070
EAN	5414363066217
Catalog Description	CBL TIE 120LB 14IN NAT NYL MNTG HOL
Long Description	Integrated Mounting Hole Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 356mm (14 Inches), Width of 7.6mm (0.3 Inches), Thickness of 2mm (0.08 Inches), Tensile Strength Rating of 534 Newtons (120 pounds), 1/4-Inch Mounting Hole

Ordering

EAN	5414363066217
UPC	786210805177

Dimensions

Product Net Width	0.301 in 7.65 mm
Product Net Depth / Length	14 in 355.6 mm

Container Information

Package Level 1 Units	50 piece
-----------------------	----------

Package Level 2 Units	500 piece
Package Level 2 Width	7.4 in 188 mm
Package Level 2 Height	7.6 in 193 mm
Package Level 2 Depth / Length	15.1 in 384 mm

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Brand / Label	Ty-Rap
Color	Natural
Effective Date	19680723
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	NYLON CABLE TIES AND ACCESSORIES

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TDS000577
Instructions and Manuals	TY537M
REACH Declaration	9AKK107992A3998
RoHS Information	9AKK107991A8069

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5044 >> Mounted Head Ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

