



Part Number : [1731140387](#)
Product Description : FCT Backshell
Connector Kit, Black Plastic Backshell, Male
Standard Density D-Sub Connector, 15
Circuits, Straight Cable Outlet, IP67
Waterproof
Series Number : 173114
Status : Active
Product Category : D-Sub Connector Kits
Engineering Number : FWH2-15P-3649



Illustration only.
The pole size may deviate from the image.

Documents & Resources

Drawings
[1731140387_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	D-Sub Connector Kits
Series	173114
Description	FCT Backshell Connector Kit, Black Plastic Backshell, Male Standard Density D-Sub Connector, 15 Circuits, Straight Cable Outlet, IP67 Waterproof
Contact Type	Machined Solder
IP Rating	IP67
Magnetic	Yes
Product Name	FCT Products
Type	Plastic, Standard Density
UPC	191130516698

Electrical

Current - Maximum per Contact	7.5A
Shield Type	None
Shielded	No

Physical

Cable Diameter	6.00-8.00mm
Circuits (Loaded)	15
Circuits (maximum)	15
Color - Resin	Red, Black
Durability (mating cycles max)	500
Gender	Male
Material - Backshell	Polyester
Material - Contact	Brass
Material - Resin	PBT
Material - Screw	Brass

Material - Seal	Elastomer
Material - Shell	Brass
Mounting Style	Locking Screw
Net Weight	25.000/g
Number of Rows	2
Orientation	Straight
Packaging Type	Bag
Pitch - Mating Interface	2.84mm
Pitch - Termination Interface	2.84mm
Plating - Backshell	None
Plating - Contact	Gold over Nickel
Plating min - Mating	0.800µm
Plating min - Termination	0.100µm
Plating - Shell	Tin
Polarized to Mating Part	Yes
Ports	1
Temperature Range - Operating	-25° to +70°C
Termination Style	Solder Cup
Thread Size	4-40 UNC
Thread Type	Standard
Tightening Test Torque	40 Ncm
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP67
Wire Size (AWG)	20