



Lighting **excellence**



@4liteuk



@4liteuk



@4lite



@4liteuk

# Pylus

Pylus Round PIR Wall Light Black

Code: 4L2/3214/PIR

**Application** Commercial

## Product Features

- Polycarbonate circular bulkhead suitable for external semi-commercial and residential applications
- CCT selectable between 3000K, 4000K and 6500K
- PIR option available
- Non-dimmable
- Fast loop-in / loop-out connections
- Body options of black or white with eyelid cover
- Polycarbonate opal diffuser
- 4 year warranty

### Technical Information

|                                         |                 |
|-----------------------------------------|-----------------|
| <b>Wattage</b>                          | 12.5W           |
| <b>Lumens Delivered</b>                 | 1100lm (4000K)  |
| <b>Lm/W</b>                             | 88lm/W (4000K)  |
| <b>Beam Angle</b>                       | 110             |
| <b>CRI</b>                              | 80              |
| <b>CCT</b>                              | 3000/4000/6000K |
| <b>Input</b>                            | 220-240V        |
| <b>Operating Temp</b>                   | -5°C - 25°C     |
| <b>SDCM</b>                             | 6               |
| <b>Product Weight without Packaging</b> | 0.413 kg        |

### Technical Information

|                            |               |
|----------------------------|---------------|
| <b>Light Source</b>        | LED           |
| <b>Colour / Finish</b>     | Black         |
| <b>IP Rating</b>           | IP54          |
| <b>Class Protection</b>    | 2             |
| <b>Internal / External</b> | External      |
| <b>Mounting Option</b>     | Ceiling, Wall |
| <b>Lumen Depreciation</b>  | L80 54,000h   |
| <b>Warranty (Years)</b>    | 4             |
| <b>CE Mark</b>             | Yes           |
| <b>Diameter</b>            | 215 mm        |
| <b>Height</b>              | 69 mm         |