



OUR OFFER

Schneider Electric Time Delay Relays RE22 Series

Schneider Electric- Time Delay Relays

RE22 Series

Stock No.	Schneider MPN	Function	Width	Voltage	Timing Range
872-5805	RE22R2AMU	On Delay	22.5 mm	24-240 V ac	0.1 s- 100 h
897-6716	RE22R1MAMR	On Delay	22.5 mm	24-240 V ac/dc	0.05 s- 300 h
896-8673	RE22R1AMR	On Delay	22.5 mm	24-240 V ac/dc	0.05 s- 300 h
896-8676	RE22R2AMR	On Delay	22.5 mm	24-240 V ac/dc	0.05 s- 300 h
897-6703	RE22R2CMR	Off Delay	22.5 mm	24-240 V ac/dc	0.05 s- 300 h
896-8698	RE22R2KMR	Off Delay	22.5 mm	24-240 V ac/dc	0.05 s- 10 min
896-8695	RE22R1KMR	Off Delay	22.5 mm	24-240 V ac/dc	0.05 s- 10 min
896-8692	RE22R1CMR	Off Delay	22.5 mm	24-240 V ac/dc	0.05 s- 300 h
897-6712	RE22R1AKMR	On & Off Delay	22.5 mm	24-240 V ac/dc	0.05 s- 300 h
897-6700	RE22R2ACMR	On & Off Delay	22.5 mm	24-240 V ac/dc	0.05 s- 300 h
897-6706	RE22R1ACMR	On & Off Delay	22.5 mm	24-240 V ac/dc	0.05 s- 300 h
872-5811	RE22R2MMW	Multi-function	22.5 mm	12-240 V ac/dc	0.1 s- 100 h
872-5817	RE22R2MMU	Multi-function	22.5 mm	24-240 V ac	0.1 s- 100 h
872-5820	RE22R2MXMU	Multi-function	22.5 mm	24-240 V ac	0.1 s- 100 h
872-5814	RE22R2MJU	Multi-function	22.5 mm	12 V ac/dc	0.1 s- 100 h
897-6725	RE22R2MYMR	Multi-function	22.5 mm	24-240 V ac	0.05 s- 300 h
897-6728	RE22R1MYMR	Multi-function	22.5 mm	24-240 V ac	0.05 s- 300 h
897-6747	RE22R1MKMR	Multi-function	22.5 mm	24-240 V ac	0.05 s- 300 h
872-5808	RE22R1QMQ	Star Delta	22.5 mm	230/380 V ac	0.1 s- 100 h
872-5801	RE22R1QMU	Star Delta	22.5 mm	24-240 V ac	0.1 s- 100 h
897-6734	RE22R2QGMR	Star Delta	22.5 mm	24-240 V ac/dc	0.05 s- 300 h
897-6731	RE22R2QTMR	Star Delta	22.5 mm	24-240 V ac/dc	0.05 s- 300 h
897-6738	RE22R1QCMU	Star Delta	22.5 mm	24-240 V ac/dc	0.05 s- 300 h
897-6740	RE22R2QEMR	Star Delta	22.5 mm	24-240 V ac/dc	0.3 s- 30 s
897-6744	RE22R2QEMT	Star Delta	22.5 mm	380-415 V ac	0.3 s- 30 s
897-6722	RE22R1MLMR	Asymmetrical	22.5 mm	24-240 V ac/dc	0.05 s- 300 h
896-8682	RE22R1DMR	Symmetrical Flashing	22.5 mm	24-240 V ac/dc	0.05 s- 300 h
896-8686	RE22R2DMR	Symmetrical Flashing	22.5 mm	24-240 V ac/dc	0.05 s- 300 h
896-8670	RE22R1HMR	Interval	22.5 mm	24-240 V ac/dc	0.05 s- 300 h
896-8689	RE22R2HMR	Interval	22.5 mm	24-240 V ac/dc	0.05 s- 300 h
897-6719	RE22R2MWMR	Interval	22.5 mm	24-240 V ac/dc	0.05 s- 300 h



For more technical information please visit:

www.rs-online.com