


FEATURES

- **Leading Edge, PWM, Trailing Edge Dimming Operation:** Offers versatile dimming options for customised lighting control
- **3.75 A Driver Current:** Provides stable current output for optimal LED performance
- **200-240 V AC Input Voltage:** Compatible with standard AC power supplies
- **IP20 Rating:** Suitable for indoor use, protecting against solid objects
- **Constant Voltage Operating Mode:** Ensures steady voltage output for consistent lighting
- **Screw Terminal Type:** Facilitates easy and secure connections

RS PRO 90W Constant Voltage LED Driver, 24V Output

RS Stock No: 642-796



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO 90W Constant Voltage LED Driver is designed to provide reliable power to LED lighting systems. With a 24V output, it ensures consistent performance for a variety of lighting applications. Ideal for both commercial and residential settings, this LED driver supports efficient energy use and long-lasting operation.

General Specifications

Dimming Operation	Leading Edge, PWM, Trailing Edge
Number of Outputs	1
Operating Modes	Constant Voltage
Primary Type	AC
Product Type	LED Driver
Sub Type	Constant Voltage LED Driver
Terminal Type	Screw

Electrical Specifications

Driver Current	3.75 A
Input Voltage	200-240 V ac
Input Voltage Type	AC
Maximum Output Power	90 W
Output Voltage	24 V

Protection Category

IP Rating	IP20
-----------	------

Approvals

Standards/Approvals	CE, EN55015, EN61000-3-2,3, EN61347-1, EN61347-2-13
---------------------	---