



SPECIALIZED JIGSAW BLADE

A-85793

Splinter-free cuts in wood, requiring no sanding. Up and down cut blade for finish on top surfaces.



TECHNICAL SPECIFICATIONS

Pack Quantity	5
Overall Length	64 mm
Plywood	5 - 65
Teeth per Inch	9
Shank	Universal
Tooth Spacing	2.8 mm

USER BENEFITS

- Very clean cut and minimal splintering. Ideal for worktops and other prestigious installations
- Symmetrical head-geometry with centring-tip for optimised results in the event of reinforcement.
- Application: Kitchens. Cabinet making. Joinery.
- Features: Unique Makita blade with two way cutting action (teeth face in opposite direction)
- Tooth Type/Set: Milled and Side Set Teeth
- ID Code: BR13

EAN 0088381149679

[Link to product - makitauk.com](https://makitauk.com)

