

## FEATURES

- **Sintered Bronze Material:** Provides high durability and wear resistance.
- **Flanged Design:** Ensures secure positioning and reduces axial movement.
- **Dynamic Load Rating of 14 N/mm<sup>2</sup>:** Suitable for applications with varying load conditions.
- **Static Load Rating of 50 N/mm<sup>2</sup>:** Capable of handling high static loads effectively.
- **ISO 2795 and ISO 9001:2008 Certified:** Meets international quality and performance standards.

## RS PRO 12.02 mm Flanged Plain Bearing

RS Stock No: 528-054



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO flanged plain bearing is designed to provide reliable performance in various industrial applications. Made from sintered bronze, it offers excellent durability and resistance to wear, making it ideal for use in environments where consistent load handling is required.

## General Specifications

Bore Size	12.02 mm
Dynamic Load Rating	14 N/mm <sup>2</sup>
Product Type	Plain Bearing
Static Load Rating	50 N/mm <sup>2</sup>
Sub Type	Flanged

## Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	15.04 mm
Width	20 mm

## Approvals

Standards/Approvals	ISO 2795, ISO 9001:2008, UKAS 001
---------------------	-----------------------------------