

Features

- 1.8m
- DVI-D Video Splitter
- Dual Link
- Constructed with UL20276 Cable
- Compliant with DVI 1.0 Specification

RS PRO 1.8m DVI-D M to 2x DV-I-D F Splitter Cable

RS Stock No: 0839487



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This 1.8m DVI-D splitter cable splits one DVI-D source to two identical output sources. This cable is for use with digital devices only.

General Specifications


Cable Type	1x DVI-D to 2x DVI-D
Connector A	DVI
Connector A Type	DVI-D Dual Link
Connector A Gender	Male
Connector B	DVI
Connector B Type	DVI-D Dual Link
Connector B Gender	Female
Connector C	DVI
Connector C Type	DVI-D Dual Link
Connector C Gender	Female
Outer Sheath Material	PVC
Sheath Colour	Beige
Size of Strands	28 AWG

Mechanical Specifications

Length	1.8m
Cable Specification	DVI 1.0 Specification
OD	8.5mm

Approvals

Standards Met	CE UKCA ROHS REACH
---------------	--------------------



P1	P2	P1	P3
1	1 BROWN	1	1 BROWN
2	2 WHITE	2	2 WHITE
3	3 SHIELD	3	3 SHIELD
4	4 RED	4	4 RED
5	5 WHITE	5	5 WHITE
6	6 RED	6	6 RED
7	7 PURPLE	7	7 PURPLE
8	8 ORANGE	8	8 ORANGE
9	9 WHITE	9	9 WHITE
10	10 SHIELD	10	10 SHIELD
11	11 YELLOW	11	11 YELLOW
12	12 WHITE	12	12 WHITE
13	13 SHIELD	13	13 SHIELD
14	14 ORANGE	14	14 ORANGE
15	15 YELLOW	15	15 YELLOW
16	16 WHITE	16	16 WHITE
17	17 GREEN	17	17 GREEN
18	18 SHIELD	18	18 SHIELD
19	19 BLUE	19	19 BLUE
20	20 WHITE	20	20 WHITE
21	21 SHIELD	21	21 SHIELD
22	22 GREY ⚠	22	22 GREY ⚠
23	23 WHITE	23	23 WHITE
24	24 SHIELD	24	24 SHIELD
25	25 SHIELD	25	25 SHIELD

NOTE: All relevant materials are complied with RoHS directive .

5&6	UL1061 26AWG INSULATOR WIRE, LENGTH 28mm,	3
	BLACK HEAT SHRINK TUBE 0.8*20mm	3
	BLACK HEAT SHRINK TUBE 2.0*4mm	28
	BLACK HEAT SHRINK TUBE 1.5*2mm	28
	BLACK HEAT SHRINK TUBE 0.8*5mm	28
	COPPER FOIL 33*90mm	3
	MOLDED PE COLOR TRANSPARENT	
4	MOLDED PVC BEIGE	
	UL20276 [(28AWG*1P+D+FAM)*7pcs+(28AWG*1PAIR)+(28AWG*3C)]+AM+AMA BRAID OD 8.5mm, JACKET BEIGE,	190mm*2
3	MOLDED THUMBSCREW #4-40, LENGTH 46.5mm, BEIGE	2
2	DVI29 FEMALE AND HEX-NUT(4.75*5.5mm) , GOLD FLASH ON CONTACTS, WHITE INSULATOR	2
1	DVI25 MALE, GOLD FLASH ON CONTACTS, BLACK INSULATOR	1
No.	DESCRIPTION	Q'TY