





TECHNIACAL SPECIFICATIONS		MALE END VIEW	FEMALE END VIEW	REV	CHG	DATE	DESCRIPTION	REVISION
HOUSING MATERIAL/COLOR	NYLON/BLACK							
CONTANCT CARRIER MATERIAL/COLOR	TPU/BLACK							
CONTACTS	BRASS/GOLD							
RECEPTACLE MATERIAL/PLATING	BRASS/NICKEL							
O-RING MATERIAL	FPM/FKM							
OPERATING CURRENT	2A(PER SIGNAL);6A(TOTAL)							
OPERATING VOLTAGE	10~30VDC							
OPERATING TEMPERATURE	-25°C~ +85°C							
PROTECTION CLASS	IEC IP67,IN MATED CONDITION							
POTTING MATERIAL	POLYURETHANE(PU)			Type of coding	Type of coding			



PROCESS BY		DATE					
CHECKED BY		DATE					
DRAWING BY	Lillian	DATE	25/06/26	Technology in connectors™			
TOLERANCE UNLESS OTHERWISE SPECIFIED	0.5-3	±0.1	UNITS	mm	DESCRIPTION: SAL-8-8FK3-16-1FS14		
	>3-6	±0.1	1st Angle Projection				
	>6-30	±0.2					
	>30-120	±0.3					
	Angle	+1°	PART NO.	42-08000	REV	A	SHEET