



PS-L3 - LED SWIVEL HEADED LANTERN



300
LUMEN
OUTPUT

10
HOURS
RUNTIME

250
METRE
BEAM RANGE

IPX4
DUST +
WATER PROOF

PS-L3RK - UNIVERSAL KIT

Rechargeable Kit including:

- PS-L3 LED Lantern
- PS-RB2LION 3.6v Li-ion 2600mAh Battery
- DC-USB-KIT Charging Kit (inc UK, EU & AUS plugs)
- 5v DC-USB Cable
- 12v USB Car Adaptor
- Carry Strap with Carabiners
- Wall Mounting Bracket



SEOUL

BEAMASTER
LENS

- 300 Lumen White Seoul® LED
- Industrial strength copolymer housing
- Optical Beamaster lens for beam penetration
- Swivel head rotation 135°
- Easy screw battery replacement
- Side charging point for use with PS-RB2LION
- Impact resistant to 1m

BATTERY 1 x 6v PJ996 Lantern Battery (not inc.)
WEIGHT 420g (without battery)
DIMENSION 170 x 115 x 255mm