

XEVOX DUPLEX PET VDS Motion Detector

BW8080



Specifications

Installation	Wall	Detection method	PIR / MW
Detection range (m)	12 x 12	Alarm memory	Yes
Immune to animals	Yes, up to 30 kg	Power consumption	13 mA
Voltage supply	9 – 16 V	Alarm contact	NC, 50 mA, 24 V DC
Tamper contact	NC, 100 mA, 24 V DC	Temperature range	–10° to 55 °C