

1	2	3	4	5	6	7	8	9	10	11
---	---	---	---	---	---	---	---	---	----	----

Drq No :- F 44630

SPECIFICATION


ACTUATING FORCE :- 11.2N MAX

RELEASE FORCE :- 3.4N MIN

SPECIAL FEATURE :-
TESTED AND STAMPED TO UL
AND CSA REQUIREMENTS

APPROVAL RATING :-
15AMPS - 250 VAC
1/3HP - 125 OR 250 VAC


DIAGRAM OF CONNECTIONS



FINAL ASSEMBLY

PACKED IN A SUITABLE PLASTIC BAG
COMPLETE WITH RS LABEL

RS STOCK NUMBER 418-3238



No OFF	ITEM No	DRG No	DESCRIPTION
2	01	F 32626	SWITCH VCF9-UL
1	02	MS 14398	FRAME & SLEEVE SA
1	03	MS 34442	PLUNGER SA
2	04	MS 15315	INSULATOR
1	05	MS 02526	LOCKNUT
2	06	MS 12572	RIVET
1	07	MS 04325	INSULATOR

SUPPLIED SEPARATELY

No OFF	DRG No	DESCRIPTION
1	MS 13236	BEZEL - TB3S
1	MS 44182	BUTTON - T3B
1	MS 44177	BUTTON - T3G
1	MS 44183	BUTTON - T3R

1	FIRST ISSUE	27/11/02
ISSUE	REVISION	DATE

<p>saia-burgess Smart solutions for comfort and safety Saia-Burgess Gateshead Limited Dukesway, Team Valley Trading Estate Gateshead, Tyne & Wear NE11 0UB Tel: +44 (0) 191 401 6100 Fax: +44 (0) 191 401 6322 www.saia-burgess.co.uk</p>	<p>THIRD ANGLE PROJECTION</p> <p>DO NOT SCALE ! THIS DRAWING MUST ONLY BE AMENDED ON A CAD SYSTEM ALL DIMENSIONS SPECIFIED IN MILLIMETRES</p>	<p>TOLERANCES UNLESS STATED:-</p> <p>NO DECIMAL PLACE ±0.50 1 DECIMAL PLACES ±0.25 2 DECIMAL PLACES ±0.15 ANGULAR ±1°</p>	APPROVED		<p>TITLE / DESCRIPTION 2VCF9T3BGR-UL</p>		
			DRAWN	T.BELL		CHECKED BY	
			DATE	27/11/02		ENGINEERING	
			SCALE	2/1		QUALITY ASSURANCE	
<p>Drq No :- F 44630</p>					<p>A3</p>		