

Datasheet

RS PRO Clear Polythene Tape

50mm x 33m

Stock number: 2205882

EN



General Description

The tape is a UV resistant, clear polythene tape with a dispersion acrylic adhesive that has been designed for professional trades. Due to its properies the tape is ideal for protection of delicate surfaces during construction and renovation.

Features

- Matt finish and excellent clarity once applied
- Clean peel from most surfaces
- Easy tear and easy to apply
- Water and UV resistant
- Abrasion resistant,
- Conformable
- Resists most common solvents

Technical Details	Typical Values
Thickness	0.11 mm
Breaking Load	25 N/cm
Elongation	300%
Adhesion to steel	1.3 N/cm
RoHS compliant	Yes
Service Temperature	- 40°C to +60°C
Application Temperature	0°C to +40°C
Storage Temperature	+12°C to +25°C

STORAGE

Tapes stored below the minimum recommended temperature will require warming up to that level before use. Up to 24 hours may be required for this to take place.