

## 40 Z 45-50

### Hook wrench

with pin

Code	ETIM
<b>6336900</b>	<b>EC011811</b>
EAN	UNSPSC
<b>4010886633694</b>	<b>27-11-17-24</b>
Country of origin	eCl@ss
<b>Germany</b>	<b>21-04-01-07</b>
Customs tariff number	
<b>82041100</b>	



### Article description

- Design according to DIN 1810 form B
- For cross-drilled nuts according to DIN 1816
- Vanadium steel 31CrV3, manganese-phosphated

### Article information

Contents (Qty of pieces)	1	Material	Vanadium steel 31CrV3
Net weight [kg]	0,136 kg	Standard	DIN 1810 - Form B
Total length [mm]	205 mm	Width across flats 1 [mm]	45-50
Total width [mm]	38 mm	Width of head 1 [mm]	6,5 mm
Total height [mm]	7 mm	Pin width/diameter	5,0 mm
Surface	manganese phosphated	Pin height	4,0 mm