


SPECIFICATION SHEET

	Product Code: 30BM24TUBE	1 pack of 10 AA3046V Plus 30 Bimetal HSS Hacksaw Blade, 24 TPI, 300 Long in a clear plastic tube										
	Product must conform to all identified criteria	SAMPLE										
DIMENSIONAL CRITERIA		SPECIFICATION	1	2	3	4	5	6	7	8	9	10
AA3046V Blades			INDIVIDUAL BLADES									
1	Colour	ECLIPSE Blue										
2	Length x Height x Thickness	300 x 12.5 x 0.63 mm										
3	Holes for Pin Diameter	4.0 mm										
4	Teeth per 25mm	24										
5	Blade meets the criteria outlined	Specification No. 6200.201										
6	Pad Print Colour	Black										
7	Pad Print Details	As Below										
8	Free from	Defects and Rust										
MULTIPLE BLADE PACKAGING												
9	100 Blades Packed in 10's in clear plastic tubes in a outer box (Approx 405 x 85 x 70 mm): The tubes have the Red Label on Right End of Box displaying following information:	ECLIPSE										
10		Flexible bimetal, Plus 30										
11		100...blades										
12		ECLIPSE, AA3046V										
13		FLEXIBLE BIMETAL										
14		HIGH SPEED STEEL										
15	24, 300 mm, 12 ins											
16	100 BLADES											
17	Date Code											
18	Pack Weight	Approx 1.900 Kg										



ECLIPSE Plus 30	CAT. No. AA3046V NEILL TOOLS LTD WWW.ECLIPSE-TOOLS.COM	FLEXIBLE BIMETAL HIGH SPEED STEEL	FOR HARD MATERIALS 3 TO 13mm THICK & SOFT MATERIALS 3 TO 6mm THICK	24 TEETH PER 25mm
------------------------	--	--------------------------------------	---	----------------------

Approved for S& J by TK / NP	Issue 2; 14 / 09 / 11	Inspection Completed by	Date
------------------------------	-----------------------	-------------------------	------