

FEATURES

- Fire Rated
- 100% Synthetic
- Food safe
- Easy to Cut

RS PRO Filter Media G4 Roll 1mx1.6m

RS Stock No.: 122-1774



price.

RS PRO Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium

Synthetic Filter Media Rolls



Product Description

Synthetic filter media rolls are easy to use, simply cut to size. The 100% polyester media is non-toxic and safe to use in all applications.

General Specifications

Filter Size Actual HxWxD (mm)	1000 x 1600 x 20 mm
Grade EN779:2012	G4
Filter Class ISO 16890	EN16890 Coarse >60%
Fibre composition Filter-Layer	PET
Colour	White
Basis Weight ISO9073-1	200g/m²
Thickness ISO9073-2	20mm
Initial Pressure Drop at 1.50m/s	47Pa
Permeability to air ISO9237	1001 l/m²s
Dust Holding Capacity	560g/m²
Flammability DIN 53438-3 DIN53438-2	F1/K1
Flammability NF P 92-502	M1
NF P92-507 NF F16-101	HL3
EN45545-2 Flammability and Smoke Toxicity	HL3
Maximum Operating Temperature	80°C
Standard Roll Sizes (m)	1x16, 1x20, 1x1.6, 1x2, 2x20, 2x3
Size Tolerances	+/-3mm



